



ITEM	QTY	DESCRIPTION	MATERIAL
1	1	Insulating plate	Glass Fiber
2	1	Cable lug	Brass
3	1	SVL link (30x5)	Tinned Copper
4	1	Earthing link (30x5)	Tinned Copper
5	2	Locking system	Stainless Steel (AISI 304)
6	4	Metallic support	Brass
7	1	Cable gland	Nikel-plated Brass
8	1	Earthing lug	Brass, Soft Yellow
9	1	Cabinet (1.5mm)	Stainless Steel (AISI 304)
10	1	Surge arrester	ZnO
11	1	Pressure compensation IP66	Stainless Steel (AISI 304)

NOTE

- Dimension in mm
- Cross section: Up to 400 sqmm
- Approx weight 14 kg

A	RE	N°	DATE	DESCRIPTION	DRAWN	APPROV
---	----	----	------	-------------	-------	--------

REVISION HISTORY

TIPO/TYPE

LBM 3/90 X

CABLE SHEATH DISCONNECTING LINK BOX WITH SVL Ur 10 kV
SYSTEM TYPE : **SINGLE-POINT BONDING**

INSTALLATION TYPE : **WALL MOUNTED**

DEGREE OF PROTECTION : **IP66**



99.535.5.1014

PROPRIETARY INFORMATION
This document contains proprietary information belonging to a Company of PRYSMIAN Group and may neither be wholly or partially reproduced nor be disclosed without written permission of PRYSMIAN SpA.